

# MICRO SIL

## *Micro Sil,*

latest generation of special addition silicone, extremely soft and precise to use.

Very high flowability, Superior dimensional stability, Heat resistance (over 200°C)  
Easy handling, Excellent detail definition,  
Can be milled, Linear variation: -0.054% (after 24 hours), No deformation in flask.

## *Characteristics*

1:1 Mixing ratio  
Biocompatible  
Final hardness 90 Shore A  
Fucsia colour

## *Applications:*

Duplication of denture moulds -Ceramics technique printed on verticulator  
Control matrix for the design of metal structures - Denture repair - Bite recording key for positioning in articulator  
Matrix for use in making temporary crowns/bridges -Matrix support for the working of metal free aesthetic materials  
Insulation of teeth/plaster in muffle.

